


DESTONER _TWO SIEVES PVS 2-7 / PVS 2-15

Machine type		PVS 2-7	PVS 2-15
Weight	kg	450	662
Power consumption	kW	2 x 0,25	2 x 0,55
Output	t.h ⁻¹	7	10 – 15
Rated current	A	2 x 1,45	
Moisture of grain	%	13 - 15	
Efficiency	%	94	70 - 80
Vibratory	- adjustable	from 30° to 70°	
Slant sieve	- adjustable	4 - 9°	
Speed flap of air regulativ	- adjustable	from 3 to	----
Concentration of solid dust harmful substance	g.m ⁻³	1 - 2	
Frequency	1.s ⁻¹	15,7	
Pressure loss	PA	1200	
Aspiration air amount	m ³ .min ⁻¹	90	140


DSEPARATION OF SMALL STONES, GLASS AND METAL PARTICLES

Destoners PVS are used for separation of small stones, glass and metal particles from grain in dry method based on different specific weight of material. They are applied in cleaning sections of flour mills. However, they can also be used for cleaning of other dry, loose and grainy materials.

DESTONER _TWO SIEVES PVS 2-7



DESTONER _TWO SIEVES PVS 2-15





**DESTONER
PVS 3**



**DESTONER
PVS 7**

Dělnická 384
530 00 Pardubice
CZECH REPUBLIC

Táňa Mičková

tel.: + 420 775 200 898

Roman Janovský

tel.: + 420 728 332 250

e-mail: torofa@email.cz

web: www.torofa.cz